



acclAIM has redefined fiber architecture, replacing cassette-based solutions with direct connections, which eliminates extra components, and cost. acclAIM delivers the lowest insertion loss available on the market, the most optical headroom, improved density, flexibility and system lifecycle. The acclAIM™ Alignment Independent Multifiber (AIM) fiber interconnect system is designed to mate multiples of 8-fiber trunk cable connectors directly to arrays of twin-fiber patch cord connectors by means of a “conversion adapter”

## Features & Benefits

### Minimize Loss – Maximize Optical Headroom

Lowest loss pre-term Solution, Minimize or eliminate need for splicing, Maximize optical headroom to overcome barriers to performance

### Design Smarter – Longer Lifecycle

Simplicity of design combined with application-defined on-site polarity adjustment, fewer components, and near-lossless performance enables acclAIM to provide a multi-generational lifecycle with a single installation of a sustainable building asset for decades to come

### Ultra-High Density Plus (UHD+)

Make the most of each rack unit (RU) with UHD+ offering more than High Density)

### Simplify Connectivity

No gender considerations – no pins, just direct connections; Direct-Mating Breakout – acclAIM connectors mate directly to an array of 2-fiber MDC duplex patch cords; Application-Defined Polarity – polarity can be adapted to nearly any link configuration; preplanned, on-site, or on the fly with no options up to 192 fibers per RU (33% to determine when ordering or designing; Improved accessibility – with the increased density of each connector and a smaller footprint enabled by acclAIM, there is more room to work on each panel

### Reduce Labor – Lower Cost

40% faster install; 60% faster removal; Single link testing after mating; Faster moves adds & changes

### Approaching Infinite Scalability

Based on the simplified design, unparalleled performance, and architecture flexibility, Infinium acclAIM has an almost limitless migration path

### Go Live Faster

Typical Total Channel Connection Loss  
 MM .45 dB, SM .40 dB

## Specifications

### General Info

Product Line	Ortronics	Country Of Origin	United States
--------------	-----------	-------------------	---------------

### Dimensions

Cable Length	40 m
--------------	------