



Wattstopper
CONTACTOR - 4 POLE NORMALLY CLOSED 120V COIL
Part No. C115NC



The Multi-pole Contactor is a compact, electrically held lighting contactor used for controlling lighting and other electrical loads in Watt Stopper Lighting Integrator (LI) lighting control panels.

Features & Benefits

| | |
|---|--|
| Multi-pole design enables control of multiple single-phase or multi-phase loads | Four pole, SPST power contacts |
| Silver cadmium oxide contacts for long life | Compatible with all HID and electronic ballast loads |
| Normally closed or normally open contacts | Accepts wire gauge #10-#14 AWG |

Specifications

General Info

| | | | |
|-----------------------|--------------|--------------------|---------------|
| Product Line | Wattstopper | Color | Black |
| UPC Number | 754182926855 | Country Of Origin | United States |
| Installation Location | Enclosure | Application Sector | Commercial |
| Standard | UL, CSA | Warranty Type | 1-Year |
| Type | Contactor | | |

Dimensions

| | | | |
|-------------------|------------|-------------------|--------|
| Product Width US | 1.7 in | Product Weight US | 0.7 lb |
| Product Volume US | 14.3 cu in | Product Depth US | 2.9 in |
| Product Height US | 2.9 in | | |

Technical Information

| | | | |
|---------------------------|---------------------------|---------------------------|----------------|
| Operating Temperature Min | 32 F | Load Rating | 30 A @ 600 VAC |
| Compatibility | LMCP Panels | Wire Gauge | 10 AWG |
| Number of Connections | 4 | Contact Configuration | N-C |
| Contact Rating | 120 V | Operating Temperature Max | 131 F |
| Number of Relays | 0 | Input Voltage | 120 V |
| Line Frequency | 50 Hz, 60 Hz | Indoor/Outdoor | Indoor |
| Mounting Type | DIN Rail | Operating Temperature | 32°-131°F |
| Operating Humidity | 5-95% RH (Non-Condensing) | Wire Connection Type | Screw Terminal |
| Storage Temperature | 23° - 176° F | | |
