



Pass and Seymour  
Discontinued - Titan Series Fluorescent 2 Wire Dimmer, White  
Part No. CDFB16W



## Features & Benefits

|  |   |
|--|---|
| For use with 2 wire 120V and 277V fluorescent dimming ballasts.            | Field configurable wall plate system.   |
| Labeling system.   | Adjustable low end output voltage.  |
| Shipped with protective film.  | Rugged construction.  |
| Superior ratings with a minimum of derating when ganged.                   | Simple to plan the rough-in.  |
| Available in single pole slide-to-OFF and single pole/3-way preset models. | Attractive European styling.  |
| Eye-catching packaging.  | Exclusive adaptor kit to install other Decorator opening devices under the Titan: wall plate system. (See Page N-29.) |
| Blank center plate included.   |   |

## Specifications

### General Info

|                   |                                      |                    |            |
|-------------------|--------------------------------------|--------------------|------------|
| Product Line      | Pass & Seymour                       | Color              | White      |
| Country Of Origin | China                                | Application Sector | Commercial |
| Standard          | cULus, California Title 24 Compliant | Type               | Dimmer     |

### Listing Agencies / 3rd Party Agencies

|              |     |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

---

Technical Information

---

|                          |  |                  |  |
|--------------------------|--|------------------|--|
| Operating Cycles         | 100                                    | Frequency Rating | 60 Hz  |
| Amperage                 | 16 A                                   | Number of Poles  | Single Pole                                  |
| Voltage                  | 120.0 V                                | Load             | Up to rating of device (including de-rating) |
| Environmental Conditions | Non-Condensing Humidity: Less than 95% |                  |  |

---