



On-Q
Discontinued - ENCLOSURE IN-WALL POWER KIT, 6FT - WHITE
Part No. CPT7526WHR6



Easily extend electrical power from an existing wall outlet to the Dual-Purpose Enclosure behind your wall-mounted TV with the Enclosure In-Wall Power Kit. This kit allows you to power your TV and AV equipment without modifying your home's electrical wiring. The pre-wired 15A tamper-resistant outlet secures into the Dual-Purpose Enclosure knockouts, enabling power and AV cables to be hidden inside the wall and out of sight. With a 6ft length, this kit provides a clean and professional installation for your home entertainment setup.

Features & Benefits

Extend electrical power from an existing wall outlet to the Legrand Dual-Purpose Enclosure behind a wall mounted TV without ever needing to modify the home's electrical wiring

Dual outlet powers multiple devices like a cable box, network switch or streaming devices

Includes everything needed to complete installation: Junction box with pre-wired outlet and 6ft in-wall rated cable, power input module, 6ft power cord, drywall saw and all necessary hardware

Pre-wired 15A Tamper Resistant outlet secures into the Dual-Purpose Enclosure knockouts allowing for power and AV cables to hide inside the wall and out of sight

Safety tested and certified power input module and 6ft in-wall rated power cable assembly

Specifications

General Info

Product Line	On-Q	Color	White
Finish	Matte	UPC Number	804428434863
Country Of Origin	China	Receptacle Type	5-15R
Number of Receptacles	2	Construction	Metal and Plastic
Included	Wall Plate	Wall Plate Type	Combination
Application Sector	Residential	Warranty Type	1-Year Limited Warranty
Type	Tamper-Resistant		

Dimensions

Product Weight US	1.16 lb	Product Depth US	3.1 in
Product Height US	11.0 in	Product Length US	8.0 in

Listing Agencies / 3rd Party Agencies

ETL Listed	Yes	ETL ListingNumber	101152094CRT-001
------------	-----	-------------------	------------------

Technical Information

Compatibility	On-Q Dual Purpose Enclosure	Seismic Tested	No
Wire Gauge	14 AWG	Cutout	3.5 inch depth required
Amperage	15 A	Indoor/Outdoor	Indoor
Number of Outlets	2		