



Pass and Seymour
15A 125V Commercial Spec-Grade Duplex Receptacle, Side Wire, Light Almond
Part No. CR15LA

Commercial Spec Grade Duplex Receptacle, Side Wire 15A 125V



Features & Benefits

- Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly. .032 inch thick, brass, triple-wipe power contacts for lasting retention.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring. Impact-resistant nylon face and thermoplastic back body.
- Accepts #14 - #10 AWG solid or stranded copper or copper-clad wire. Terminal compartments isolated from each other for positive conductor containment.
- Auto-ground clip assures positive ground. For covering patents, see www.legrand.us/patents.
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#). Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +50°C, minimum -40°C without impact

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
Number of Receptacles	2	Outlet Type	Commercial, Indoor
Application Sector	Commercial	Standard	UL498, CSA C22.2 No. 42
Warranty Type	1-Year Limited Warranty	Type	Outlet

Dimensions

Product Width US	1.322 in	Product Depth US	0.78 in
------------------	----------	------------------	---------

Product Height US	2.635 in
-------------------	----------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Dielectric Strength	Withstands 1500V minimum	Connection	Side wire
---------------------	--------------------------	------------	-----------

Number of Wires	3	Temperature Rating	-40° - 50° C
-----------------	---	--------------------	--------------

Amperage	15 A	Number of Poles	Double Pole
----------	------	-----------------	-------------

Wire Size	14 - 10 AWG	Indoor/Outdoor	Indoor
-----------	-------------	----------------	--------

Voltage	125.0 V	Environmental Conditions	Flammability: UL94 V2
---------	---------	--------------------------	-----------------------
