



The Pass & Seymour series of corrosion-resistant cord connectors feature a body and compression nut made of Type 304 stainless steel with exceptional tensile strength and the highest levels of durability in severely corrosive environments. All stainless steel cord grips include an embedded Buna-N O-Ring. These connectors are recommended for use in washdowns or high moisture environments in food processing plants, petrochemical facilities, wastewater treatment plants, pulp & paper mills and chemical manufacturing factories. (Note: Type 316 stainless steel also available upon request and minimums may apply.)

Features & Benefits

304 grade Stainless Steel construction provides exceptional tensile strength and resists corrosion and impacts

The combination tightening surface provides a large wrenching area for easy installation

Also available in 316 grade stainless steel, upon request. Minimums may apply

Includes an embedded Buna-N O-Ring providing a long term seal and protection against ingress

Available in straight male from 3/8" to 3" NPT

Specifications

General Info

UPC Number 785007107821

Country Of Origin United States

Product Line Pass & Seymour

Application Sector Commercial/Industrial

Construction Stainless Steel Cord Grip

Standard UL Listed, CSA Listed

Technical Information

Cable Size 2.81 - 3.00