



Pass and Seymour
Stainless Steel Strain Relief Cord Grip, 1/2-in Straight, .50-.56 OD Range
Part No. CGSS50562M



Stainless Steel Strain Relief Cord Grips are woven of stainless steel mesh with a Type 304 stainless steel body for corrosion resistance. They are offered in single/double weave construction to help absorb direct pull, to resist flexing and binding, and to eliminate strain. They are recommended for indoor or outdoor use where subjected to moisture and corrosion in the wiring of pendant stations, processing equipment, hand tools, and power cord sets.

Features & Benefits

304 grade Stainless Steel body and mesh construction provides exceptional tensile strength and resists corrosion and impacts

The combination tightening surface provides a large wrenching area for easy installation

Also available in 316 grade stainless steel, upon request. Minimums may apply

Includes an embedded Buna-N O-Ring providing a long-term seal and protection against ingress

Available in straight male fittings from 1/2 : 3/4 to 3 : NPT

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007107920
Country Of Origin	United States	Construction	Stainless Steel Cord Grip
Application Sector	Commercial/Industrial	Standard	UL Listed, CSA Listed

Technical Information

Maximum Cable Range	0.5 in	Minimum Cable Range	0.56 in
---------------------	--------	---------------------	---------