



Pass and Seymour

Discontinued - Construction Spec Grade Smooth Face Receptacles, Back and Side Wire, 15A, 125V, Light Almond

Part No. CRB5262SLA

Construction Spec Grade Smooth Face Duplex Receptacle Back & Side Wire 15amp 125volt Light Almond

Features & Benefits

Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly.

.032 inch thick, brass, triple-wipe power contacts for lasting retention.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

Impact-resistant nylon face and thermoplastic back body.

8 hole internal screw-pressure-plate back wire terminals accept #10 - #14 AWG solid or stranded copper or copper-clad conductors.

Terminal compartments isolated from each other for positive conductor containment.

Tri-drive terminal and mounting screws.

Auto-ground clip assures positive ground.

Smooth face version features an impact-resistant nylon face for ease of cleaning and less dirt build-up.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	United States
Application Sector	Residential/Commercial	Standard	UL 498

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Phase	3	Number of Wires	3
Amperage	15 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Voltage	125.0 V