



Construction Spec Grade Smooth Face Duplex Receptacle Back and Side-Wire 20A 125V

## Features & Benefits

Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly.	.032 inch thick, brass, triple-wipe power contacts for lasting retention.
Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.	Impact-resistant nylon face and thermoplastic back body.
8 hole internal screw-pressure-plate back wire terminals accept #10 - #14 AWG solid or stranded copper or copper-clad conductors.	Terminal compartments isolated from each other for positive conductor containment.
Tri-drive terminal and mounting screws.	Auto-ground clip assures positive ground.
Smooth face version features an impact-resistant nylon face for ease of cleaning and less dirt build-up.	For covering patents, see <a href="http://www.legrand.us/patents">www.legrand.us/patents</a> .
For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click <a href="#">here</a> .	Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007307337	Country Of Origin	United States
Application Sector	Commercial, Residential	Standard	UL 498, FEDSPEC

### Dimensions

Product Width US	1.322 in	Product Depth US	0.78 in
Product Height US	2.635 in	Product Length US	1.0E-4 in

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Phase	Three	Number of Wires	3
Amperage	20 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG		