



Pass and Seymour
15A 125V Commercial Spec-Grade Duplex Receptacle, Back and Side Wire, Black
Part No. CRB5262BK



Construction Spec Grade Duplex Receptacle Back and Side Wire 15A 125V

Features & Benefits

- Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly.

Impact-resistant nylon face and thermoplastic back body.

Terminal compartments isolated from each other for positive conductor containment.

For covering patents, see www.legrand.us/patents.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.
Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

8 hole internal screw-pressure-plate back wire terminals accept #10 - #14 AWG solid or stranded copper or copper-clad conductors.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info			
Product Line	Pass & Seymour	Color	Black
UPC Number	785007210187	Country Of Origin	Mexico
Number of Receptacles	2	Application Sector	Commercial
Standard	UL498, CSA C22.2 No. 42, FEDSPEC	Warranty Type	1-Year Limited Warranty

Type	Outlet		
Dimensions			
Product Width US	1.322 in	Product Depth US	0.78 in
Product Height US	2.635 in		
Listing Agencies / 3rd Party Agencies			
cULus Listed	Yes		
Technical Information			
Dielectric Strength	Withstands 2000V minimum	Connection	Back and side wire
Number of Wires	3	Temperature Rating	-40° - 60° C
Amperage	15 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Indoor/Outdoor	Indoor
Environmental Conditions	Flammability: UL94 V2		