



Construction 1-Pole Switch, Back and Side-Wire, 15A 120/277V.

## Features & Benefits

One-piece brass alloy contact arm for reliable electrical performance.

High strength thermoplastic polycarbonate toggle resists breaking and chipping under heavy abuse.

Back body made of glass-reinforced nylon. Locking support provides resistance to face and back body separation.

Cam designed for fast make with positive break action to minimize arcing and prolong switch life.

Tri-drive terminal and mounting screws.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

One-piece steel strap with integral ground is plated for corrosion resistance.

Heavy-duty toggle bumpers for smooth and quiet operation.

Available with side wire or external screw-pressure-plate back and side wire models capable of accepting #14 - #10 AWG copper or copper-clad wire.

Oversized silver alloy contacts for longer dependable switch life.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

|                   |                |                    |              |
|-------------------|----------------|--------------------|--------------|
| Product Line      | Pass & Seymour | Color              | Brown        |
| Finish            | Matte          | UPC Number         | 785007126006 |
| Country Of Origin | Mexico         | Application Sector | Commercial   |
| Standard          | UL 20, FEDSPEC |                    |              |

### Dimensions

|                                       |                   |                           |             |
|---------------------------------------|-------------------|---------------------------|-------------|
| Product Width US                      | 1.32 in           | Product Depth US          | 1.073 in    |
| Product Height US                     | 3.281 in          |                           |             |
| Listing Agencies / 3rd Party Agencies |                   |                           |             |
| cULus ListingNumber                   | 140597            | cULus Listed              | Yes         |
| Technical Information                 |                   |                           |             |
| Contact Rating                        | 15Amp, 120/277Vac | Closed Contact Resistance | Toggle      |
| Amperage                              | 15 A              | Number of Poles           | Single Pole |
| Wire Size                             | #14 - #10 AWG     | Wattage                   | 1 W         |