



Wattstopper
Resi PIR Vacancy Sensor, 2-wire, White
Part No. CS-50-W



The CS-50 Passive Infrared (PIR) Vacancy Sensor provides automatic shutoff for single-pole lighting control applications. It is engineered to comply with specific provisions of California's Title 24-2013 energy code.

Features & Benefits

Collection consolidated to white option

LED status indicator

Two-wire sensor; no neutral connection

Manual-on/automatic-off control

Adjustable time delay

Specifications

General Info

Product Line	Wattstopper	Color	White
Finish	Glossy	UPC Number	754182926923
Country Of Origin	China	Product Series	CS-50
Features	Adjustable Time Delay, Indicator Lights	Switch Type	Push
Installation Location	Wall	Included	Mounting Screws, Wire Nuts
Application Sector	Commercial, Residential	Standard	UL, cUL, California Title 24 Compliant
Warranty Type	5-Year	Type	Sensor, Switch

Dimensions

Product Width US	1.8 in	Product Weight US	0.2095 lb
------------------	--------	-------------------	-----------

Product Volume US	23.805 cu in	Product Depth US	1.4 in
-------------------	--------------	------------------	--------

Product Height US	4.1 in
-------------------	--------

Technical Information

Operating Temperature Min	32 °F	Timer Type	Trimpot
---------------------------	-------	------------	---------

Load Rating	600 W @ 120 VAC	Has Battery	No
-------------	-----------------	-------------	----

Sensor Coverage Pattern	180 deg	Sensor Type	Vacancy
-------------------------	---------	-------------	---------

Operating Temperature Max	131 °F	Number of Gangs	1
---------------------------	--------	-----------------	---

Sensor Mounting Height	4 ft	Number of Buttons	1
------------------------	------	-------------------	---

Number of Rockers	0	Sensor Technology	Passive Infrared (PIR)
-------------------	---	-------------------	------------------------

Timer Duration	30 Seconds, 5-30 Minutes	Number of Poles	Single Pole
----------------	--------------------------	-----------------	-------------

Indicator	PIR Detection LED	Input Voltage	120 V
-----------	-------------------	---------------	-------

Line Frequency	60 Hz	Indoor/Outdoor	Indoor
----------------	-------	----------------	--------

Sensor Coverage	600 sq ft	Mounting Type	In-Wall
-----------------	-----------	---------------	---------

On Function	Manual On	Operating Temperature	0°-55°C, 32°-131°F
-------------	-----------	-----------------------	--------------------

Operating Humidity	5-95% RH (Non-Condensing)	Sensing Range	24 x 25 ft
--------------------	---------------------------	---------------	------------

Wire Connection Type	Flying Leads	Engraving Type	Blank
----------------------	--------------	----------------	-------

Storage Temperature	23° - 176° F, -5° - 80° C
---------------------	---------------------------
