



Pass and Seymour  
Commerical 20A Specification Grade Toggle Switch, Gray  
Part No. CS20AC3GRY



Commercial 3-Way Switch, Side-Wire, 20A 120/277V. These switches offer excellent value while meeting federal specification standards. External screw-pressure-plate back wiring enables fast installation and superior electrical connections. Rugged construction shrugs off hard use and abuse.

## Features & Benefits

One-piece brass alloy contact arm for reliable electrical performance.

High strength thermoplastic polycarbonate toggle resists breaking and chipping under heavy abuse.

Back body made of glass-reinforced nylon. Locking support provides resistance to face and back body separation.

Cam designed for fast make with positive break action to minimize arcing and prolong switch life.

Tri-drive terminal and mounting screws.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

One-piece steel strap with integral ground is plated for corrosion resistance.

Heavy-duty toggle bumpers for smooth and quiet operation.

Available with side wire or external screw-pressure-plate back and side wire models capable of accepting #14 - #10 AWG copper or copper-clad wire.

Oversized silver alloy contacts for longer dependable switch life.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

|                    |                |                   |  |
|--------------------|----------------|-------------------|--|
| Product Line       | Pass & Seymour | Color             | Gray   |
| Finish             | Matte          | Country Of Origin | Mexico   |
| Application Sector | Commercial     | Standard          | UL Listed E140597,<br>Standard UL20,<br>FedSpec WS896,<br>Flammability Rating<br>UL94 V2 |
| Type               | Switch         |                   |  |

Dimensions

|                   |          |                  |          |
|-------------------|----------|------------------|----------|
| Product Width US  | 1.32 in  | Product Depth US | 1.073 in |
| Product Height US | 3.281 in |                  |          |

Listing Agencies / 3rd Party Agencies

|                     |        |              |     |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 140597 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Technical Information

|                       |  |                       |                                 |
|-----------------------|--|-----------------------|---------------------------------|
| Contact Configuration | One piece brass alloy contact arm                                    | Actuator              | Toggle                          |
| Connection            | locking support, one piece brass alloy contact arm, Back & Side wire | Contact Rating        | Oversized silver alloy contacts |
| Amperage              | 20 A   | Number of Poles       | 3-Way                           |
| Indoor/Outdoor        | Indoor   | Operating Temperature | -40°-115°C                      |
| Voltage               | 120/277 V  | Connection Type       | Wired                           |
| Degree of Protection  | 1500V Dielectric Withstand Voltage                                   |                       |                                 |