



Pass and Seymour
Flexcor® Turnlok® EHU Strain Relief Grips, Cable Diameter 0.22 - 0.32 in.
Part No. FC22GL



FC22GL: Extra-Hard Use, Closed Mesh, Cable Diameter 0.22 - 0.32 inches,
Mesh Length 4.5-in

Features & Benefits

EHU wire mesh grips provide additional strain-relief for wiring device plugs and connectors used on portable equipment in commercial and institutional applications, and industrial plant and construction site areas, which incur abnormally high abuse.

Support grips are woven of corrosion-resistant tinned-stainless steel wire.

Most Flexcor products have UL and/or CSA approvals. Please contact factory for approval information.

Mesh Length: 4.00

Specifications

General Info

| | | | |
|--------------|---|--------------------|------------|
| Product Line | Pass & Seymour | Country Of Origin | Mexico |
| Construction | Support and Strain Relief Grips, Various Types of Pulling | Application Sector | Industrial |
| Standard | UL/CSA Approval (consult factory) | | |

Dimensions

| | | | |
|-------------------|---------|------------------|--------|
| Product Width US | 0.32 in | Product Depth US | 4.5 in |
| Product Height US | 0.32 in | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|------------|-----|-----------------|-------|
| CSA Listed | Yes | CSA File Number | 67507 |
|------------|-----|-----------------|-------|

Technical Information

| | | | |
|---------------------|---------|---------------------|---------|
| Maximum Cable Range | 0.22 in | Minimum Cable Range | 0.32 in |
|---------------------|---------|---------------------|---------|

| | | | |
|----------|--|----------|--|
| Capacity | Various Cable Diameter Ranges | Mounting | Consult the Factory for Mounting Recommendations |
| Load | Strain Relief Grips are designed to prevent tension from being transferred to junctions and terminals on electrical cord, cable and conduit, therefore providing a more secure electrical structure. | | |