



Wattstopper
High/Low PIR Fixture Mount Sensor w/flying leads
Part No. FS-305-D



The FS-305 PIR occupancy sensor turns lighting on and off automatically based on occupancy. It is a low voltage, low profile device, designed for installation inside the bottom of either an indoor or outdoor lighting fixture body.

Features & Benefits

IP65 and UL 244A and 508 rated (when fully assembled and installed) for use in wet location environments (indoor and outdoor)

Fixed sensitivity optimized for FS-LxW and FS-L6 lens coverages

Polycarbonate, flame retardant, UV resistant, impact resistant (FS-LxW lenses)

Recyclable

Specifications

General Info

Product Line	Wattstopper	Color	White
UPC Number	754182931200	Country Of Origin	China
Product Series	FS-305	Features	Adjustable Time Delay, Dimming, Impact Resistant, Indicator Lights, Light Level Sensor, Power Pack Required, Recyclable, UV Resistant
Installation Location	Fixture	Included	Spacer
Standard	UL, cUL	Warranty Type	5-Year
Type	Sensor		

Dimensions

Product Width US	1.4 in	Product Weight US	0.1 lb
------------------	--------	-------------------	--------

Product Volume US	4.7 cu in	Product Depth US	1.4 in
Product Height US	2.4 in		
Technical Information			
Operating Temperature Min	-40 °F	Has Battery	No
Sensor Type	Occupancy	Operating Temperature Max	131 °F
Sensor Mounting Height	8-40 ft	Sensor Technology	Passive Infrared (PIR)
Input Voltage	12 to 30 VDC	Mounting Type	Fixture Embedded, Threaded Collar
On Function	Auto On	Current Draw	6.5 mA
Operating Temperature	-40°-131°F, -40°-55°C	Operating Humidity	5-95% RH (Non-Condensing)
Wire Connection Type	Flying Leads	Storage Temperature	-40° - 176° F, -40° - 80° C