



Wattstopper Fixture Mount Sensor Low Voltage w/RJ-45 connection Part No. FS-305RC



The FS-305 and FS-355 are PIR occupancy sensors that turn lighting on and off automatically based on occupancy. The models are slim, low-profile devices designed for installation inside the bottom of either an indoor or outdoor lighting fixture body.

Features & Benefits

Low-profile fixture integrated sensor

Adjustable time delay

Line and low voltage models

Multiple lens choices

IP65 rated for indoor and outdoor wet locations

Daylighting light level feature

Specifications

General Info

Product Line	Wattstopper	Color	White
Finish	Glossy	UPC Number	754182930975
Country Of Origin	China	Product Series	FS-305
Features	Adjustable Time Delay, Impact Resistant, Indicator Lights, Light Level Sensor, Power Pack Required, Recyclable, UV Resistant	Installation Location	Fixture
Included	Spacer	Application Sector	Commercial
Standard	UL, cUL	Warranty Type	5-Year
Type	Sensor		

Dimensions

Product Width US	1.5 in	Product Weight US	0.2 lb
------------------	--------	-------------------	--------

Product Volume US	26.7 cu in	Product Depth US	1.3 in
-------------------	------------	------------------	--------

Product Height US	2.4 in
-------------------	--------

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Operating Temperature Min	-40 °F	Timer Type	Trimpot
---------------------------	--------	------------	---------

Has Battery	No	Sensor Type	Occupancy
-------------	----	-------------	-----------

Operating Temperature Max	131 °F	Sensor Mounting Height	8-40 ft
---------------------------	--------	------------------------	---------

Sensor Technology	Passive Infrared (PIR)	Timer Duration	30 Seconds, 5-30 Minutes
-------------------	------------------------	----------------	--------------------------

Input Voltage	12 to 30 VDC	Indoor/Outdoor	Indoor
---------------	--------------	----------------	--------

Mounting Type	Fixture Embedded, Threaded Collar	On Function	Auto On
---------------	-----------------------------------	-------------	---------

Current Draw	6.5 mA	Operating Temperature	-40°-131°F, -40°-55°C
--------------	--------	-----------------------	-----------------------

Operating Humidity	5-95% RH (Non-Condensing)	Wire Connection Type	RJ-45
--------------------	---------------------------	----------------------	-------

Storage Temperature	-40° - 176° F, -40° - 80° C
---------------------	-----------------------------
