



Wattstopper's ELCU-200 Emergency Lighting Control Unit is a self-contained device that allows any standard lighting control device to control emergency lighting in conjunction with normal lighting in any area within a building.

Features & Benefits

- Eliminates energy waste caused by emergency lighting that is always on Integral push-to-test button activates emergency mode for a true test condition
- Connects to EMTS-100 Remote Test Switch or other input to activate emergency on from a remote location Operates as a control device or as a shunt
- Senses local single circuit power failure Zero cross switching technology for reliability and increased product life
- Compatible with Wattstopper occupancy sensors, daylighting controls, lighting control panels, and dimmers

Specifications

General Info

Product Line	Wattstopper	Color	White
UPC Number	754182919567	Country Of Origin	United States
Installation Location	Ceiling, Wall	Application Sector	Commercial
Standard	UL 924, NEC, OSHA, NFPA 101	Warranty Type	5-Year
Type	Test Switch		

Dimensions

Product Width US	2.9 in	Product Weight US	0.1 lb
------------------	--------	-------------------	--------

Product Volume US	18.5 cu in	Product Depth US	1.3 in
-------------------	------------	------------------	--------

Product Height US	4.9 in
-------------------	--------

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Operating Temperature Min	32 F	Compatibility	ELCU-100, ELCU-200
---------------------------	------	---------------	--------------------

Contact Configuration	N-C	Contact Rating	24 VDC
-----------------------	-----	----------------	--------

Operating Temperature Max	131 F	Number of Relays	0
---------------------------	-------	------------------	---

Input Voltage	24 VDC	Indoor/Outdoor	Indoor
---------------	--------	----------------	--------

Mounting Type	Wall	Operating Temperature	32°-131°F
---------------	------	-----------------------	-----------

Operating Humidity	5-95% RH (Non-Condensing)	Wire Connection Type	Flying Leads
--------------------	---------------------------	----------------------	--------------

Storage Temperature	23° - 176° F
---------------------	--------------
