




On-Q
17-in Dual-Purpose In-Wall Enclosure
Part No. ENP1700NA



The 17-in Dual-Purpose In-Wall Enclosure is engineered to provide storage of structured wiring and AV components. The ENP1700NA is constructed of Wi-Fi transparent material to manage wireless components and AV devices at point-of-use locations, like directly behind a TV or other media centers. It can also be used for structured wiring purposes, as smaller-sized options in the existing line of On-Q enhanced structured wiring enclosures. The ENP1700NA is compatible with devices like the Samsung One Connect Box, Apple TV, Roku, Amazon Fire TV, network switches, 3rd party structured wiring components and more. Includes a split cover, trim ring and drywall clips, allowing for both new construction and retrofit installations.

Features & Benefits

Designed for in-wall storage and distribution of structured wiring and AV components

Can be placed behind most TV wall-mounts including SANUS premium TV mounts

Compatible with devices like the Samsung One Connect Box, Apple TV, Roku, Amazon Fire TV, 3rd party structured wiring components and more

Trim ring conceals drywall cut out for clean finish and smooth transition to wall surface

Split cover is low profile and designed to snap into place. Split design supports removal and access to components even if partially covered

Knockout configurations support conduit and in-wall wired connections, while a cable pass through on cover allows for outside cable connections

Features (2) AC knockouts to accommodate a single gang junction box to power devices in enclosure

Universal mounting grid maximizes compatibility with 3rd party devices without additional mounting brackets

Features drywall clips to allow both retrofit and new construction installations

UL Listed and constructed of Wi-Fi transparent ABS plastic to ensure uninterrupted performance of wireless devices

Proudly made in the USA

Specifications

General Info

Product Line	On-Q	Color	White
UPC Number	804428434146	Country Of Origin	United States
Application Sector	Residential/Commercial	Standard	RoHS, UL, cULus
Type	Enclosure		

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Additional Information

RoHS Conformant Yes Prop 65 Warning Required Yes

Prop 65 Warning Language □ WARNING: This product can expose you to Tetrabromobisphenol A, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov.

Technical Information

Compatibility Paintable with Rust-Oleum paint for plastic or equivalent Thickness 0.1 in

Frame Injection-molded plastic Operating Temperature 32 to 122 F

Mounting Consult the Factory for Mounting Recommendations Environmental Conditions 0 to 93 (relative humidity, non-condensing) pct
