



Wattstopper Ultrasonic Fixture Mount Sensor, Wall Mount Part No. FS-555



FS-555



FS-555C

The FS-555 and FS-555C Line Voltage Ultrasonic Fixture Sensors control lighting based on occupancy. They are designed with a low-profile, architecturally pleasing appearance to easily integrate into a wide range of lighting fixtures or a customized housing.

Features & Benefits

Line voltage for direct connection to load

Easily integrate into lighting fixtures

Ideal for stairwell, wall and ceiling mount applications

Ultrasonic technology for open area detection with line-of-sight obstructions

Ceiling and wall mount models

Specifications

General Info

Product Line	Wattstopper	Color	White
Finish	Glossy	UPC Number	754182931255
Country Of Origin	China	Product Series	FS-555
Features	Adjustable Time Delay, Flame Retardant, Indicator Lights, Sensitivity Adjustment	Installation Location	Fixture, Wall
Included	Mounting Screws	Application Sector	Commercial
Standard	UL, cUL, RoHS	Warranty Type	5-Year
Type	Sensor		

Dimensions

Product Width US	6.125 in	Product Weight US	3.584 oz
------------------	----------	-------------------	----------

Product Volume US	10.46 cu in	Product Depth US	1.265 in
Product Height US	1.35 in		
Additional Information			
RoHS Compliant	Yes		
Technical Information			
Operating Temperature Min	32 °F	Timer Type	Trimpot
Load Rating	4.9 A @ 120/277 VAC	Has Battery	No
Sensor Type	Occupancy	Operating Temperature Max	131 °F
Sensor Mounting Height	8-10 ft	Sensor Technology	Ultrasonic
Timer Duration	30 Seconds, 5-30 Minutes	Indicator	Ultrasonic Detection LED
Input Voltage	120/277 VAC	Line Frequency	60 Hz
Indoor/Outdoor	Indoor	Mounting Type	Fixture Embedded, Mounting Slots, Screw Holes
On Function	Auto On	Current Draw	43 mA
Operating Temperature	0°-55°C, 32°-131°F	Operating Humidity	5-95% RH (Non-Condensing)
Wire Connection Type	Flying Leads	Storage Temperature	-40° - 176° F, -40° - 80° C