



The Q-Series fiber enclosure system is designed to support standard density applications in building networks. The all steel chassis enables reliable protection and management of fiber optic cable patching, splicing, and connecting. The enclosure also enables distribution of backbone cabling to active equipment, switching, or cross/interconnect horizontal area. The footprint accommodates up to 72 LC fibers in a 1 RU space, accepting OFP adapter panels, M2 pre-terminated cassettes, and splice cassettes

## Features & Benefits

### Highly Accessible:

Front and rear doors along with removable top panels give appreciable access to the enclosure when patching and dressing cables

### Versatile Installation:

Compatible with OFP adapter panels, M2 pre-terminated cassettes and M2 splice cassettes • Removable Top Covers: Tool-less, 60/40 split-top design allows for easy access from above

Max number of fibers per RU (SC)

36

Max number of fibers per RU (12F MPO)

288

Cassette / Adapter panels per RU

3

### Simplified Installation:

The rack-mount brackets feature an open-ended ear design to allow the enclosure to rest on pre-mounted screws in the rack for a one-person installation

### Removable Top Covers:

Tool-less, 60/40 split-top design allows for easy access from above

Max number of fibers per RU (LC)

72

Max number of fibers per RU (24F MPO)

576

## Specifications

### General Info

Color	Black	UPC Number	662875019954
-------	-------	------------	--------------

Country Of Origin	China	Product Line	Legrand
-------------------	-------	--------------	---------

Type	Enclosure
------	-----------

### Technical Information

Mounting	Rack Mount	Compatibility	OFP/M2/LM2
----------	------------	---------------	------------

---

Durability

OFP/M2/LM2

Capacity

72 LC Fibers

---

Gauge

18

Rack Units

1U

---

Frame

Steel

---