



Ortronics
4 RU Q-Series Standard Density Rack-Mount Fiber Enclosure
Part No. EQ04U-CVC



The 4U Q-Series Standard Density (SD) footprint fiber enclosure system is designed to support standard density applications in building networks. The all-steel chassis enables reliable protection and management of fiber optic cable patching, splicing, and connecting. The enclosure also enables distribution of backbone cabling to active equipment, switching, or cross/interconnect horizontal area. The footprint accommodates up to 72 fibers with LC connectivity and 144 fibers with MDC per Rack Unit (RU), or a maximum capacity of 288 fibers LC and 576 MDC (VSFF), utilizing OFP adapter panels, LM2 pre-terminated cassettes, and M2 splice cassettes.

Features & Benefits

Highly Accessible: Front and rear doors along with removable top panels give appreciable access to the enclosure when patching and dressing cables

Simplified Installation: The rack-mount brackets feature an open-ended ear design to allow the enclosure to rest on pre-mounted screws in the rack for a one-person installation

Versatile Installation: Compatible with OFP adapter panels, M2 pre-terminated cassettes and M2 splice cassettes - Removable Top Covers: Tool-less, 60/40 split-top design allows for easy access from above

Removable Top Covers: Tool-less, 60/40 split-top design allows for easy access from above

Max number of fibers per RU (SC): 36

Max number of fibers per RU (LC): 72

Max number of fibers per RU (12F MPO): 288

Max number of fibers per RU (24F MPO): 576

Cassette / Adapter panels per RU: 3

Specifications

General Info

Product Line	Ortronics	Color	Black
UPC Number	662875020004	Country Of Origin	Mexico
Features	Drawer Slide, Removable Cover	Application Sector	Commercial, Industrial
Type	Enclosure		

Dimensions

Product Width US	17.12 in	Product Depth US	19.13 in
------------------	----------	------------------	----------

Product Height US 7.0 in

Technical Information

Fiber Optic Cable Type	OM3, OM4, OM5	Compatibility	LM2, M2, OFP
------------------------	---------------	---------------	--------------

Rack Units	4	Gauge	18
------------	---	-------	----

Capacity	12 Adapter Panels, 12 Cassettes	Mounting	Rack Mount
----------	---------------------------------	----------	------------
