



Wattstopper
Discontinued - High/Low/Off PIR Outdoor Fixture Sensor, Straight Nipple, 20 ft lens, 120-480V, Bronze
Part No. FSP-221B-S-L3-BR



The FSP-2x1B sensors provide multi-level control based on motion and/or daylight contribution. They control 0-10 VDC LED drivers or dimming ballasts, as well as non-dimming ballasts and, with an FSP-Lx Lens, are rated for wet and cold locations. All control parameters are adjustable via a wireless configuration tool capable of storing and transmitting sensor profiles. The FSP-2x1B family is available in three configurations for mounting inside a fixture, to the outside of a fixture via a 1/2" knockout, or to a pole.

Features & Benefits

| | |
|---|---|
| Designed for LED fixtures and rated for extreme temperatures; options for box or pole mounting | Fully adjustable high and low dimmed light levels |
| Hold off setpoint with automatic calibration option for convenience and added energy savings | Adjustable via handheld wireless configuration tool |
| IP66 rated with choice of lenses for wet and outdoor locations, and mounting heights from 8' to 40' | Adjustable time delay and cutoff delay |

Specifications

General Info

| | | | |
|-------------------|-------------|------------|--------------|
| Product Line | Wattstopper | UPC Number | 754182940127 |
| Country Of Origin | China | | |

Dimensions

| | | | |
|-------------------|--------------|-------------------|----------|
| Product Width US | 5.608 in | Product Weight US | 0.531 lb |
| Product Volume US | 34.484 cu in | Product Depth US | 2.419 in |
| Product Height US | 2.542 in | | |

Additional Information

| | |
|-------------------------------|-----|
| Product Environmental Profile | Yes |
|-------------------------------|-----|

Technical Information

| | | | |
|-------------|---------------------|-------------------|-------------------------------------|
| Sensor Type | Daylight, Occupancy | Sensor Technology | Passive Infrared (PIR), Photosensor |
|-------------|---------------------|-------------------|-------------------------------------|