



**Wattstopper**  
**0-10V PIR DROP MT SENSOR BLE 1 20-480V 20FT LENS - GREY**  
Part No. FSP-321B-D-L3-G



The FSP-3x1B sensors provide continuous dimming light level control based on motion and/or daylight contribution. They control 0-10 VDC LED drivers or dimming ballasts, as well as non-dimming ballasts and, with an FSP-Lx Lens, are rated for wet and cold locations. All control parameters are adjustable via the iOS or Android Sensor Configuration App capable of storing and transmitting sensor profiles. The FSP-3x1B family is available in three configurations for mounting inside a fixture, to the outside of a fixture via a 1/2" knockout, or to a pole.

## Features & Benefits

Designed for LED fixtures and rated for extreme temperatures; options for box or pole mounting

Fully adjustable high and low dimmed light levels

Hold off setpoint with automatic calibration option for convenience and added energy savings

Continuous dimming & daylight harvesting for energy efficiency and energy code compliance

Adjustable via the iOS® or Android® Sensor Configuration App

IP66 rated with choice of lenses for wet and outdoor locations, and mounting heights from 8' to 40'

Adjustable time delay and cutoff delay

## Specifications

### General Info

|                   |  |                       |              |
|-------------------|--|-----------------------|--------------|
| Product Line      | Wattstopper  | Color                 | Gray         |
| Finish            | Glossy   | UPC Number            | 754182941537 |
| Country Of Origin | China  | Product Series        | FSP-3x1B     |
| Features          | Adjustable Time Delay, Flame Retardant, Impact Resistant, Light Level Sensor, Recyclable, Sensitivity Adjustment, UV Resistant | Installation Location | Pole         |
| Included          | Collar   | Application Sector    | Commercial   |
| Standard          | UL, cUL, CE, TUV Listed, IP66 Rated, RoHS, E101196, PEP  | Warranty Type         | 5-Year       |
| Type              | Sensor   |                       |              |

---

## Dimensions

---

|                   |              |                   |          |
|-------------------|--------------|-------------------|----------|
| Product Width US  | 5.818 in     | Product Weight US | 0.576 lb |
| Product Volume US | 57.111 cu in | Product Depth US  | 2.419 in |
| Product Height US | 4.058 in     |                   |          |

---

## Additional Information

---

|                |     |
|----------------|-----|
| RoHS Compliant | Yes |
|----------------|-----|

---

## Technical Information

---

|                           |  |                        |                                 |
|---------------------------|--|------------------------|---------------------------------|
| Operating Temperature Min | -40 °F   | Timer Type             | Digital                         |
| Load Rating               | 1200 W @ 277 VAC, 1200 W @ 347/480 VAC, 300 W @ 230-240 VAC, 800 W @ 120 VAC | Compatibility          | Bluetooth                       |
| Has Battery               | No   | Horsepower Rating      | 1/6 HP @ 120/277 VAC            |
| Sensor Coverage Pattern   | 360 deg  | Sensor Type            | Daylight, Occupancy             |
| Operating Temperature Max | 140 °F   | Sensor Mounting Height | 20 ft                           |
| Sensor Technology         | Passive Infrared (PIR), Photosensor  | Timer Duration         | 30 Seconds, 5-30 Minutes        |
| Indicator                 | PIR Detection LED  | Input Voltage          | 100 to 347 VAC, 208/230/480 VAC |
| Line Frequency            | 50 Hz, 60 Hz   | Indoor/Outdoor         | Both                            |
| Mounting Type             | Drop Nipple, Fixture Embedded  | On Function            | Auto On                         |
| Operating Temperature     | -40°-140°F, -40°-60°C  | Operating Humidity     | 5-95% RH (Non-Condensing)       |
| Sensing Range             | 40 ft diameter   | Wire Connection Type   | Flying Leads                    |
| Storage Temperature       | -40° - 176° F, -40° - 80° C  |                        |                                 |

---