




## Legrand

5' Alternating USB Steel Plugmold® Multioutlet System  
Part No. G20GB509TRUSBA



Available in 5' (1.5m) length with 9" spacing. 15A tamper-resistant receptacles. 3-wire, #12 THHN (1 hot, 1 neutral and insulated ground conductor). .040" (1.0 mm) steel housing. Packed two per carton. Each unit supplied with one (1) Coupling and two (2) Blank End Fittings. USB is 2.4 Amps (shared between two ports) 5VDC. Please note the charging load on one module will not affect the charging performance of the other USB modules in the product.

### Features & Benefits

USB charging. Dual-port charging modules share 2.4 amps of charging capacity and can charge multiple phones, tablets or other mobile devices at the same time.

Multiple colors and finishes. Painted finishes of black, gray, ivory, and white, as well as anodized aluminum and stainless steel versions integrate easily with any room decor.

Compact design. Low-profile design installs in tight locations while offering multiple power and USB charging connections. Receptacle spacing accommodates bulky AC adapters.

Tamper-resistant receptacles. Prevents the insertion of foreign objects into receptacles reducing the risk of shocks or electrocution. Meets 2014 NEC section 406 requirements.

### Specifications

#### General Info

UPC Number	786776184440
Countries Of Origin	United States
Product Line	Wiremold
Application Sector	Commercial
Type	Plugmold
Number of Receptacles	6
Standard	cULus Listed Multioutlet Assembly: File E15191 Guide PVGT

#### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
cULus ListingNumber	E15191

#### Buy American Act Compliance

NAFTA	Yes
-------	-----

#### Additional Information

RoHS Conformant	Yes
-----------------	-----

