



Wattstopper
High Bay Sensor 24VDC w/360 Degree Lens for 20ft MH
Part No. HB300B-L3

The HB3x0B-Lx PIR occupancy sensors are designed for automatic lighting control in warehouses and other indoor high bay spaces. They are modular and are made up of two parts, a Power Module (HB3x0-B) and a Lens (HBLx), sold separately or in prepackaged combinations. The lenses are specifically engineered to provide reliable coverage from a wide range of mounting heights.



Features & Benefits

Lens & sensor will be offered separately

Integrated occupancy sensor and lens device

Easy mounting with snap-in mounting hardware

Lens choices for mounting between 20-40 feet

Line or low voltage

Specifications

General Info

Product Line	Wattstopper	Color	White
Finish	Glossy	UPC Number	754182936243
Country Of Origin	China	Product Series	High Bay
Features	Adjustable Time Delay, Sensitivity Adjustment	Installation Location	Ceiling, Fixture
Included	Back Box, Lens	Application Sector	Commercial
Standard	UL, RoHS	Warranty Type	5-Year
Type	Sensor		

Dimensions

Product Width US	4.0 in	Product Weight US	0.4 lb
Product Volume US	43.3 cu in	Product Depth US	4.16 in

Product Height US	2.6 in
-------------------	--------

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Operating Temperature Min	32 °F	Timer Type	DIP Switch
---------------------------	-------	------------	------------

Compatibility	BZ Power Packs	Has Battery	No
---------------	----------------	-------------	----

Sensor Coverage Pattern	360 deg	Sensor Type	Occupancy
-------------------------	---------	-------------	-----------

Operating Temperature Max	158 °F	Sensor Mounting Height	20 ft
---------------------------	--------	------------------------	-------

Number of Buttons	0	Number of Rockers	0
-------------------	---	-------------------	---

Sensor Technology	Passive Infrared (PIR)	Timer Duration	15 Seconds, 5-30 Minutes
-------------------	------------------------	----------------	--------------------------

Input Voltage	24 VDC	Indoor/Outdoor	Indoor
---------------	--------	----------------	--------

Mounting Type	Fixture Embedded	On Function	Auto On
---------------	------------------	-------------	---------

Current Draw	11 mA	Operating Temperature	0°-70°C, 32°-158°F
--------------	-------	-----------------------	--------------------

Operating Humidity	20-95% RH (Non-Condensing)	Sensing Range	40 ft diameter
--------------------	----------------------------	---------------	----------------

Wire Connection Type	Flying Leads	Engraving Type	Blank
----------------------	--------------	----------------	-------

Connection Type	Wired	Storage Temperature	23° - 176° F, -5° - 80° C
-----------------	-------	---------------------	---------------------------
