



Wattstopper
High Bay Occupancy Sensor For Wet Locations, 347/480 V, 60 Hz, w/IR, w/extender module
Part No. HB340W



HB3x0W-Lx occupancy sensors are designed for automatic lighting control in warehouses and other medium and high bay wet location applications. They are modular and are made up of two parts, a Power Module (HB3x0W) and a Lens (HBLxW), sold separately or in prepackaged combinations. These components are designed to work as a convenient system. Different models offer a choice of coverage patterns for a range of applications.

Features & Benefits

IP65 rated for wet locations

Multiple mounting options for easy installation

Lens choices for mounting between 20-40 feet

Line or low voltage

Specifications

General Info

Product Line	Wattstopper	Color	White
Finish	Glossy	UPC Number	754182924035
Country Of Origin	China	Product Series	High Bay
Features	Adjustable Time Delay, Sensitivity Adjustment	Installation Location	Fixture
Included	Extender Module	Application Sector	Commercial
Standard	UL, RoHS	Warranty Type	5-Year
Type	Sensor		

Dimensions

Product Width US	4.1 in	Product Weight US	0.4 lb
Product Volume US	35.8 cu in	Product Depth US	4.6 in
Product Height US	1.9 in		

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Operating Temperature Min	32 °F	Timer Type	DIP Switch
Load Rating	1200 W @ 347/480 VAC	Has Battery	No
Response Frequency	60 Hz	Sensor Type	Occupancy
Operating Temperature Max	158 °F	Number of Buttons	0
Sensor Technology	Passive Infrared (PIR)	Timer Duration	15 Seconds, 5-30 Minutes
Input Voltage	347/480 VAC	Line Frequency	60 Hz
Indoor/Outdoor	Indoor	Mounting Type	Fixture Embedded
On Function	Auto On	Operating Temperature	0°-70°C, 32°-158°F
Operating Humidity	20-95% RH (Non-Condensing)	Wire Connection Type	Flying Leads
Engraving Type	Blank	Connection Type	Wired
Storage Temperature	23° - 176° F, -5° - 80° C		