




Wiremold
5' Alternating USB Steel Plugmold® Multioutlet System
Part No. G20GB509TRUSBA



Available in 5' (1.5m) length with 9" spacing. 15A tamper-resistant receptacles. 3-wire, #12 THHN (1 hot, 1 neutral and insulated ground conductor). .040" (1.0 mm) steel housing. Packed two per carton. Each unit supplied with one (1) Coupling and two (2) Blank End Fittings. USB is 2.4 Amps (shared between two ports) 5VDC. Please note the charging load on one module will not affect the charging performance of the other USB modules in the product.

Features & Benefits

USB charging. Dual-port charging modules share 2.4 amps of charging capacity and can charge multiple phones, tablets or other mobile devices at the same time.

Compact design. Low-profile design installs in tight locations while offering multiple power and USB charging connections. Receptacle spacing accommodates bulky AC adapters.

Multiple colors and finishes. Painted finishes of black, gray, ivory, and white, as well as anodized aluminum and stainless steel versions integrate easily with any room decor.

Tamper-resistant receptacles. Prevents the insertion of foreign objects into receptacles reducing the risk of shocks or electrocution. Meets 2014 NEC section 406 requirements.

Specifications

General Info

Product Line	Wiremold	Color	Gray
UPC Number	786776184440	Country Of Origin	United States
Product Series	2000 Series	Number of Receptacles	3
Features	USB-A Charging	Outlet Type	Tamper-Resistant
Application Sector	Commercial, Education, Entertainment, Healthcare, Hospitality, Retail	Standard	cULus Listed Multioutlet Assembly: File E15191 Guide PVGT
Warranty Type	1-Year from Installation or 2-Years from Day of Sale	Type	Plugmold
Installed Devices	Single Receptacle, USB-A Ports		

Dimensions

Product Width US	1.3 in	Product Weight US	2.04 lb
Product Depth US	0.75 in	Product Length US	1.3 in
Receptacle Spacing	9 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E15191	cULus Listed	Yes
---------------------	--------	--------------	-----

Additional Information

RoHS Compliant	Yes	Product Environmental Profile	Yes
----------------	-----	-------------------------------	-----

Technical Information

Is Pre-Wired	Yes	USB Wattage	15 W
USB Amperage	2.4 A	Wiring Configuration	Single Circuit
Number of USBs	3	Amperage	15 A
Indoor/Outdoor	Indoor	Wiring Method	Hard-Wired
NEMA Configuration Code	5-15R	Mounting Type	On Surface
Voltage	125.0 V	Environmental Conditions	Dry interior locations