



## Wattstopper High Bay Occupancy Sensor For Wet Locations, 120/277V, 60Hz, w/IR Part No. HB350W



HB3x0W-Lx occupancy sensors are designed for automatic lighting control in warehouses and other medium and high bay wet location applications. They are modular and are made up of two parts, a Power Module (HB3x0W) and a Lens (HBLxW), sold separately or in prepackaged combinations. These components are designed to work as a convenient system. Different models offer a choice of coverage patterns for a range of applications.

### Features & Benefits

IP65 rated for wet locations

Multiple mounting options for easy installation

Lens choices for mounting between 20-40 feet

Line or low voltage

### Specifications

#### General Info

Product Line	Wattstopper	Color	White
Finish	Glossy	UPC Number	754182924042
Country Of Origin	China	Product Series	High Bay
Features	Adjustable Time Delay, Sensitivity Adjustment	Installation Location	Fixture
Included	Extender Module	Application Sector	Commercial
Standard	UL, RoHS	Warranty Type	5-Year
Type	Sensor		

#### Dimensions

Product Width US	4.1 in	Product Weight US	0.4 lb
Product Volume US	35.8 cu in	Product Depth US	4.6 in

---

Product Height US	1.9 in
-------------------	--------

---

### Additional Information

---

RoHS Compliant	Yes
----------------	-----

---

### Technical Information

---

Operating Temperature Min	32 °F	Timer Type	DIP Switch
---------------------------	-------	------------	------------

---

Load Rating	1200 W @ 277 VAC, 800 W @ 120 VAC	Has Battery	No
-------------	-----------------------------------	-------------	----

---

Response Frequency	60 Hz	Sensor Type	Occupancy
--------------------	-------	-------------	-----------

---

Operating Temperature Max	158 °F	Number of Buttons	0
---------------------------	--------	-------------------	---

---

Number of Rockers	0	Sensor Technology	Passive Infrared (PIR)
-------------------	---	-------------------	------------------------

---

Timer Duration	15 Seconds, 5-30 Minutes	Input Voltage	120/277 VAC
----------------	--------------------------	---------------	-------------

---

Line Frequency	60 Hz	Indoor/Outdoor	Indoor
----------------	-------	----------------	--------

---

Mounting Type	Fixture Embedded	On Function	Auto On
---------------	------------------	-------------	---------

---

Operating Temperature	0°-70°C, 32°-158°F	Operating Humidity	20-95% RH (Non-Condensing)
-----------------------	--------------------	--------------------	----------------------------

---

Wire Connection Type	Flying Leads	Engraving Type	Blank
----------------------	--------------	----------------	-------

---

Connection Type	Wired	Storage Temperature	23° - 176° F, -5° - 80° C
-----------------	-------	---------------------	---------------------------

---