




Wiremold
5' Alternating USB Steel Plugmold® Multioutlet System
Part No. G20GB509TRUSBA



Available in 5' (1.5m) length with 9" spacing. 15A tamper-resistant receptacles. 3-wire, #12 THHN (1 hot, 1 neutral and insulated ground conductor). .040" (1.0 mm) steel housing. Packed two per carton. Each unit supplied with one (1) Coupling and two (2) Blank End Fittings. USB is 2.4 Amps (shared between two ports) 5VDC. Please note the charging load on one module will not affect the charging performance of the other USB modules in the product.

Features & Benefits

USB charging. Dual-port charging modules share 2.4 amps of charging capacity and can charge multiple phones, tablets or other mobile devices at the same time.

Compact design. Low-profile design installs in tight locations while offering multiple power and USB charging connections. Receptacle spacing accommodates bulky AC adapters.

Multiple colors and finishes. Painted finishes of black, gray, ivory, and white, as well as anodized aluminum and stainless steel versions integrate easily with any room decor.

Tamper-resistant receptacles. Prevents the insertion of foreign objects into receptacles reducing the risk of shocks or electrocution. Meets 2014 NEC section 406 requirements.

Specifications

General Info

| | | | |
|--------------------|---------------|-----------------------|---|
| Product Line | Wiremold | UPC Number | 786776184440 |
| Country Of Origin | United States | Number of Receptacles | 6 |
| Application Sector | Commercial | Standard | cULus Listed Multioutlet Assembly: File E15191 Guide PVGT |
| Type | Plugmold | | |

Dimensions

| | | | |
|------------------|---------|-------------------|---------|
| Product Width US | 1.3 in | Product Weight US | 2.04 lb |
| Product Depth US | 0.75 in | Product Length US | 1.3 in |

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | E15191 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Additional Information

| | | | |
|----------------|-----|-------------------------------|-----|
| RoHS Compliant | Yes | Product Environmental Profile | Yes |
|----------------|-----|-------------------------------|-----|

Technical Information

| | | | |
|----------|------|----------------|-------|
| Amperage | 20 A | Enclosure Type | Steel |
|----------|------|----------------|-------|

| | | | |
|---------|---------|--------------------------|------------------------|
| Voltage | 125.0 V | Environmental Conditions | Dry interior locations |
|---------|---------|--------------------------|------------------------|
