



radiant Collection  
radiant® Multi-Location Remote Dimmer, White  
Part No. HMRW



Provides precise dimming control of a light or fixture from another part of the room through this second on-wall controller. Must be used with the Multi-Location Master Dimmer. Part of the radiant® Collection, it also features clean lines and smooth control for a sophisticated touch. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

## Features & Benefits

- Installs easily with 3-way wiring for multi-location dimming. For use with most Incandescent, CFL/LED (with the exception of 0 - 10v options) and MLV dimmable bulbs.
- Low-profile paddle switch offers smoother On/Off control, while a separate, ergonomic slider allows you to adjust light levels with precision.
- Constant memory features returns lights to their previous level after a power failure or outage.
- No derating required in multi-gang applications.
- Features durable, high-impact resistant thermoplastic construction.
- More color options available. (For Tri-Color version: Includes three interchangeable face plates in white, light almond, and ivory for flexible customization.)
- Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007039719
Country Of Origin	China	Features	Color Change Kit, High-End Trim (Dim Range), Locator Light, Low-End Trim (Dim Range)
Switch Type	Digital, Multi-Location, Paddle, Single Pole 3-Way	Number of Switches	1

Application Sector	Residential	Standard	UL Listed
Warranty Type	Limited Lifetime Warranty	Type	Dimmer
Dimensions			
Product Width US	1.75 in	Product Depth US	1.25 in
Product Height US	4.25 in		
Listing Agencies / 3rd Party Agencies			
cULus Listed	Yes		
Technical Information			
Load Rating	120V 450W (CFL), 120V 450W (LED), 120V 700VA (MLV), 120V 700W (Halogen), 120V 700W (Incandescent)	Dimming Compatibility	Forward Phase
Frequency Rating	60 Hz	Number of Gangs	1
Minimum Load Recommendation	6 W	Bulb Compatibility	CFL, Incandescent, LED
Number of Poles	Multi-Location, Single Pole 3-Way	Wire Size	#14 - #10 AWG
Trim/Adjustment Level	Button	Requires Neutral Wire	No
Indoor/Outdoor	Indoor	Mounting Type	Wall Box
Wire Connection Type	Screw Terminals	Voltage	120 VAC
Environmental Conditions	Humidity: Less than 95% non condensing		