



Wiremold
GFCI PLUGMOLD 6FT GRAY 11 OUTLETS AND SELF TEST GFCI MOD
Part No. G20GB606TRGFI6



Plugmold® Multioutlet Systems are available in a wide variety of lengths and fittings and in a variety of finishes to provide versatile solutions for many applications. Plugmold options include single or alternating circuits, standard or isolated ground receptacles, GFCI protection, tamper-resistant protection, USB charging, Snapicoil® harnesses of prewired receptacles, and cord-ended units. Plugmold® Multioutlet Systems are available in black or ivory ScuffCoat™ finish, painted white or gray enamel steel, stylish stainless steel, anodized aluminum and durable textured ivory nonmetallic. The painted steel product works with many types of decor and is paintable to integrate with most color schemes. Durable stainless steel and anodized aluminum Plugmold products are corrosion-resistant, making them ideal for labs.

Features & Benefits

Compact, low profile appearance. Enhanced aesthetics and ideal for installations within minimal spaces.

Specifications

General Info

| | | | |
|--------------------|---------------|-----------------------|--|
| Product Line | Wiremold | UPC Number | 786776188059 |
| Country Of Origin | United States | Number of Receptacles | 11 |
| Application Sector | Commercial | Standard | cULus Listed Multioutlet assemblies: File E15191 Guide PVGT. Meets Article 380 of NEC. |
| Type | Plugmold | | |

Dimensions

| | |
|-------------------|---------|
| Product Weight US | 3.78 lb |
|-------------------|---------|

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | E15191 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Additional Information

| | |
|----------------|-----|
| RoHS Compliant | Yes |
|----------------|-----|

Technical Information

| | | | |
|----------|---------|--------------------------|------------------------|
| Amperage | 20 A | Enclosure Type | Steel |
| Voltage | 125.0 V | Environmental Conditions | Dry interior locations |