



Wattstopper High Bay Control Module, 208/240 VAC, Power Module & Mounting Box Part No. HB330-B



The HB3x0B-Lx PIR occupancy sensors are designed for automatic lighting control in warehouses and other indoor high bay spaces. They are modular and are made up of two parts, a Power Module (HB3x0-B) and a Lens (HBLx), sold separately or in prepackaged combinations. The lenses are specifically engineered to provide reliable coverage from a wide range of mounting heights.

Features & Benefits

Integrated occupancy sensor and lens device
Lens choices for mounting between 20-40 feet

Easy mounting with snap-in mounting hardware
Line or low voltage

Specifications

General Info

Product Line	Wattstopper	Color	White
Finish	Glossy	UPC Number	754182923199
Country Of Origin	China	Product Series	High Bay
Features	Adjustable Time Delay, Sensitivity Adjustment	Installation Location	Ceiling, Fixture
Included	Back Box	Application Sector	Commercial
Standard	UL, RoHS	Warranty Type	5-Year
Type	Sensor		

Dimensions

Product Width US	4.0 in	Product Weight US	0.4 lb
Product Volume US	33.1 cu in	Product Depth US	4.16 in
Product Height US	2.0 in		

Additional Information

RoHS Compliant Yes

Technical Information

Operating Temperature Min 32 °F Timer Type DIP Switch

Load Rating 5 A @ 240 VAC Has Battery No

Sensor Type Occupancy Operating Temperature Max 158 °F

Number of Buttons 0 Number of Rockers 0

Sensor Technology Passive Infrared (PIR) Timer Duration 15 Seconds, 5-30 Minutes

Input Voltage 208/240 VAC Line Frequency 60 Hz

Indoor/Outdoor Indoor Mounting Type Fixture Embedded

On Function Auto On Operating Temperature 0°-70°C, 32°-158°F

Operating Humidity 20-95% RH (Non-Condensing) Wire Connection Type Flying Leads

Engraving Type Blank Storage Temperature 23° - 176° F, -5° - 80° C
