



Wattstopper High Bay Low Voltage Sensor, 347/480VAC Power Part No. HB340



The HB3x0B-Lx PIR occupancy sensors are designed for automatic lighting control in warehouses and other indoor high bay spaces. They are modular and are made up of two parts, a Power Module (HB3x0-B) and a Lens (HBLx), sold separately or in prepackaged combinations. The lenses are specifically engineered to provide reliable coverage from a wide range of mounting heights.

Features & Benefits

Integrated occupancy sensor and lens device

Easy mounting with snap-in mounting hardware

Lens choices for mounting between 20-40 feet

Line or low voltage

Specifications

General Info

Product Line	Wattstopper	Color	White
Finish	Glossy	UPC Number	754182920358
Country Of Origin	China	Product Series	High Bay
Features	Adjustable Time Delay, Sensitivity Adjustment	Installation Location	Ceiling, Fixture
Application Sector	Commercial	Standard	UL, RoHS
Warranty Type	5-Year	Type	Sensor

Dimensions

Product Width US	4.0 in	Product Weight US	0.24 lb
Product Volume US	11.8 cu in	Product Depth US	4.16 in
Product Height US	0.7 in		

Additional Information

RoHS Compliant Yes

Technical Information

Operating Temperature Min	32 °F	Timer Type	DIP Switch
Load Rating	5 A @ 347/480 VAC	Has Battery	No
Sensor Type	Occupancy	Operating Temperature Max	158 °F
Number of Buttons	0	Sensor Technology	Passive Infrared (PIR)
Timer Duration	15 Seconds, 5-30 Minutes	Input Voltage	347/480 VAC
Line Frequency	60 Hz	Indoor/Outdoor	Indoor
Mounting Type	Fixture Embedded	On Function	Auto On
Current Draw	11 mA	Operating Temperature	0°-70°C, 32°-158°F
Operating Humidity	20-95% RH (Non-Condensing)	Wire Connection Type	Flying Leads
Engraving Type	Blank	Storage Temperature	23° - 176° F, -5° - 80° C