



Wattstopper High Bay Occupancy Sensor For Wet Locations, 120/277V, w/IR, w/20 ft mounting height lens Part No. HB350W-L3



HB3x0W-Lx occupancy sensors are designed for automatic lighting control in warehouses and other medium and high bay wet location applications. They are modular and are made up of two parts, a Power Module (HB3x0W) and a Lens (HBLxW), sold separately or in prepackaged combinations. These components are designed to work as a convenient system. Different models offer a choice of coverage patterns for a range of applications.

Features & Benefits

IP65 rated for wet locations	Multiple mounting options for easy installation
Lens choices for mounting between 20-40 feet	Line or low voltage

Specifications

General Info

Product Line	Wattstopper	Color	White
Finish	Glossy	UPC Number	754182270590
Country Of Origin	China	Product Series	High Bay
Features	Adjustable Time Delay, Sensitivity Adjustment	Installation Location	Fixture
Included	Extender Module, Lens	Application Sector	Commercial
Standard	UL, RoHS	Warranty Type	5-Year
Type	Sensor		

Dimensions

Product Width US	4.1 in	Product Weight US	0.6 lb
Product Volume US	37.7 cu in	Product Depth US	4.6 in
Product Height US	2.0 in		

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Operating Temperature Min	32 °F	Timer Type	DIP Switch
---------------------------	-------	------------	------------

Load Rating	1200 W @ 277 VAC, 800 W @ 120 VAC	Has Battery	No
Sensor Coverage Pattern	360 deg	Response Frequency	60 Hz
Sensor Type	Occupancy	Operating Temperature Max	158 °F
Sensor Mounting Height	20 ft	Number of Buttons	0
Number of Rockers	0	Sensor Technology	Passive Infrared (PIR)
Timer Duration	15 Seconds, 5-30 Minutes	Input Voltage	120/277 VAC
Line Frequency	60 Hz	Indoor/Outdoor	Indoor
Mounting Type	Fixture Embedded	On Function	Auto On
Operating Temperature	0°-70°C, 32°-158°F	Operating Humidity	20-95% RH (Non-Condensing)
Sensing Range	40 ft diameter	Wire Connection Type	Flying Leads
Engraving Type	Blank	Connection Type	Wired
Storage Temperature	23° - 176° F, -5° - 80° C		