



Wattstopper
High Bay - 300 High Density Sensor Lens 360 Degrees, 40Ft Mounting Height
Part No. HBL7



Legrand's HBL7 lens module works with the HB3x0 series sensor to provide automatic lighting control. For high bay applications, the HBL7 is designed for mounting at heights between 20' to 40', with coverage area up to 100' in diameter when mounted at 40'. The HBL7 is ideal for high ceiling open area and aisleway coverage in high bay applications.

Features & Benefits

Ideal for high ceiling open area and aisleway coverage in high bay applications All are multi-cell, multi-tier Fresnel lenses
100' diameter coverage when mounted at a 40' height

Specifications

General Info

Product Line	Wattstopper	Color	White
UPC Number	754182940608	Country Of Origin	China
Product Series	HBLx	Features	Flame Retardant, Impact Resistant, Recyclable, UV Resistant
Installation Location	Ceiling	Standard	RoHS
Warranty Type	5-Year	Type	Lens

Dimensions

Product Width US	3.6 in	Product Weight US	1.1 oz
Product Volume US	13.4 cu in	Product Depth US	3.72 in
Product Height US	1.0 in		

Technical Information

Operating Temperature Min	32 °F	Has Battery	No
Sensor Coverage Pattern	360 deg	Sensor Type	Occupancy
Operating Temperature Max	131 °F	Sensor Mounting Height	40 ft
Sensor Technology	Passive Infrared (PIR)	Indoor/Outdoor	Indoor
Mounting Type	Sensor	Operating Temperature	0°-55°C, 32°-131°F
Operating Humidity	5-95% RH (Non-Condensing)	Sensing Range	100 ft diameter
