

Shielded HDJ systems are ideal for installations with high levels of interference and offer flexibility with a easy, quick-to-install design



Features & Benefits

Circuit traces: Each circuit trace is rated to 100W, 1.5A	Superior Protection Against EMI: Minimizes disturbances in data transmission
Enhances PoE heat dissipation: Ideal for high-power PoE applications	Accepts color ID icons: Perfect for port identification or segmentation
Versatile mounting: Use at both ends of the channel, compatible with patch panels, wall plates, furniture plates, surface mount boxes and more	High density footprint: Mount up to 48 ports per 1RU
Rear loading: Preferred mounting for panels	Plenum Rated to UL 2043: Can be installed in any air handling space
Lacing Cap Design: No punch tool required, quick termination and installation time.	Always Ready for Install: Each package of jacks includes 1 standard lacing cap termination tool (Compatible with any HDJ or KT2 jacks).
Enhanced ergonomics: Optional high durability metal, lacing cap termination tool makes install easier, improving bulk installation and sustainability. Part Number: HDJHCT	Replacement plastic lacing cap termination tools, part number: HDJPCT-4PK

Specifications

General Info

Product Line	Ortronics	UPC Number	662875020035
Country Of Origin	Mexico	Application Sector	Commercial, Industrial
Standard	UL Standard	Type	Jack

Dimensions

Product Width US

0.63 in

Product Depth US

1.61 in

Product Height US

0.77 in

Additional Information

RoHS Compliant

Yes
