



Pass and Seymour

Isolated Ground Heavy Duty Spec Grade Single Receptacles, Back and Side Wire, 20A, 125V, Orange

Part No. IG5361

Isolated Ground Heavy-Duty Spec Grade Single Receptacle Back and Side-Wire 20A 125V



## Features & Benefits

IG symbol and Isolated Ground markings for easy identification and circuit delineation.

High-impact resistant nylon face resists impacts and scrapes.

Patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.

Side and internal screw-pressure-plate back wire capability with #14 - #10 AWG copper or copper-clad, solid or stranded wire.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.

Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Triple-wipe brass contacts ensure lasting, positive contact with plug blades.

Corrosion-resistant plated steel strap.

Plastic barrier isolates grounding terminal from mounting strap and metal boxes.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Orange
UPC Number	785007653618	Country Of Origin	Mexico
Application Sector	Commercial	Standard	UL498, CSA C22.2 No. 42, FEDSPEC

---

## Dimensions

---

Product Width US	1.38 in	Product Depth US	1.093 in
------------------	---------	------------------	----------

---

Product Height US	1.68 in
-------------------	---------

---

## Listing Agencies / 3rd Party Agencies

---

cUL ListingNumber	140596	cUL Listed	Yes
-------------------	--------	------------	-----

---

## Technical Information

---

Dielectric Strength	Withstands 2000V minimum	Connection	Back and side wire
---------------------	--------------------------	------------	--------------------

---

Number of Wires	3	Temperature Rating	-40° - 60° C
-----------------	---	--------------------	--------------

---

Amperage	20 A	Number of Poles	Double Pole
----------	------	-----------------	-------------

---

Wire Size	14 - 10 AWG	Environmental Conditions	Flammability: UL94 V2
-----------	-------------	--------------------------	-----------------------

---