



Isolated Ground Heavy-Duty Spec Grade Duplex Receptacle Back and Side Wire 15A 125V

Features & Benefits

- IG symbol and Isolated Ground markings for easy identification and circuit delineation. Face color coding by voltage facilitates locating and mating of proper devices.
- High-impact resistant nylon face resists impacts and scrapes. Corrosion-resistant plated steel strap.
- Patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation. Plastic barrier isolates grounding terminal from mounting strap and metal boxes.
- Auto-ground clip assures positive ground. For covering patents, see www.legrand.us/patents.
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#). Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

| | | | |
|-----------------------|----------------------------------|--------------------|------------|
| Product Line | Pass & Seymour | Color | Red |
| UPC Number | 785007045314 | Country Of Origin | Mexico |
| Number of Receptacles | 2 | Application Sector | Commercial |
| Standard | UL498, CSA C22.2 No. 42, FEDSPEC | Type | Outlet |

Dimensions

| | | | |
|------------------|----------|------------------|----------|
| Product Width US | 1.322 in | Product Depth US | 0.922 in |
|------------------|----------|------------------|----------|

Product Height US 2.635 in

Listing Agencies / 3rd Party Agencies

cULus ListingNumber 140596 cULus Listed Yes

Technical Information

Dielectric Strength Withstands 2000V minimum Connection Back and side wire

Number of Wires 3 Temperature Rating -40° - 60° C

Amperage 15 A Number of Poles Double Pole

Wire Size 14 - 10 AWG Indoor/Outdoor Indoor

Environmental Conditions Flammability: UL94 V2
