



Pass and Seymour

20A 125V Heavy Duty Hospital-Grade Isolated Ground Duplex Receptacle, Back and Side Wire, Light Almond

Part No. IG8300LA

Isolated Ground Heavy-Duty Hospital Grade Duplex Receptacle Back and Side Wire 20A 125V



Features & Benefits

IG symbol and Isolated Ground markings for easy identification and circuit delineation.

Corrosion-resistant plated steel strap.

Plastic barrier isolates grounding terminal from mounting strap and metal boxes. Auto-ground clip assures positive ground.

For covering patents, see www.legrand.us/patents.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

High-impact resistant nylon face resists impacts and scrapes.

Patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	United States
Number of Receptacles	2	Outlet Type	Commercial, Indoor
Application Sector	Commercial	Standard	UL498, CSA C22.2 No. 42
Warranty Type	1-Year Limited Warranty	Type	Outlet

Dimensions

Product Width US	1.322 in	Product Depth US	0.922 in
Product Height US	2.635 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Dielectric Strength	Withstands 2000V minimum	Connection	Back and side wire
---------------------	--------------------------	------------	--------------------

Number of Wires	3	Temperature Rating	-40° - 60° C
-----------------	---	--------------------	--------------

Amperage	20 A	Number of Poles	Double Pole
----------	------	-----------------	-------------

Wire Size	14 - 10 AWG	Indoor/Outdoor	Indoor
-----------	-------------	----------------	--------

Voltage	125.0 V	Environmental Conditions	Flammability: UL94 V2
---------	---------	--------------------------	-----------------------
