

Turnlok Single Receptacle 4wire 20amp 125/250volt Isolated Ground



Features & Benefits

UL1449 (latest revision). [1.2 x 50: s 6000V, 8 x 20: s 3000A].

9,000 amps current handling capability in each of three modes: line to neutral, line to ground, neutral to ground.

Nominal let-through (suppressed) voltage in all 3 modes, 500V.

Response time less than 1 nanosecond for unmounted MOV.

Electronic components potted for electrical, mechanical and thermal stability.

Leakage current: 0.5 mA at 25: C/120VAC.

Common mode noise attenuation: 500 KHz to 30 MHz: up to 35 dB[50 ohm source impedance]

Operating temperature: -40: C to 85: C[-40: F to 185: F] Conforms to the latest revision ANSI/IEEE C62.41 (formerly IEEE 587), ANSI/IEEE C62.45.

140 joules of energy absorption in each of the three modes.

1 filtering capacitor for 7 to 1 average noise reduction.

LED indicator light.

Overcurrent protection in all 3 modes.

Thermal protection in all 3 modes.

3 18mm super MOVs to suppress transients in all modes : equally.

Varistor voltage: 150V RMS. Back and side wire capability including ground terminal.

Specifications

General Info

Color Orange

UPC Number 785007142099

Countries Of Origin Mexico

Product Line Pass & Seymour

Application Sector Industrial

Standard UL Listed

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

cULus ListingNumber 140596

Technical Information

Number of Poles	3-Way
Voltage	125 V
Phase	3
Number of Wires	4
