



Pass and Seymour  
20A 125V Isolated Ground Surge Protective Duplex Receptacle, Back and Side Wire, Gray  
Part No. IG5362GRYSP



Isolated Ground Surge Protective Duplex Receptacle offers increased transient protection, reliability and protection notification (Audible Alarm with LED Indicator). Back and Side Wire, 20A, 125V

## Features & Benefits

Solid-state LED monitor has 25-year minimum life expectancy. A high visibility, wide-angle lens .032 inch thick, brass, triple-wipe power contacts for lasting retention. indicates protection is in place.

Audible alarm alert of MOV damage. Alarm able to be turned On/Off. Wrap-around steel strap for structural integrity. Auto-ground is standard, for easier installation.

Triple-wipe, copper-alloy contacts for superior, more dependable connection. External screw-pressure-plate back and side wire terminals including ground with external back wire clamps (exclusive) accept #14 - #10 AWG copper or copper-clad, solid or stranded conductors.

External pressure plate feature allows two conductors to be terminated by a single screw. Plastic barrier isolates grounding terminal from mounting strap and metal boxes.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007194081	Country Of Origin	Mexico
Application Sector	Commercial	Standard	cUL UL1449, UL498: CSA C22.2 No. 42: ANSI/IEEE C62.41 (Formerly IEEE 587), ANSI/IEEE C62.45 Installation Categories "A" (Ring Wave) "B" (Unidirectional Impulse).

### Dimensions

Product Width US	1.75 in	Product Depth US	1.225 in
Product Height US	2.8 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	140596	cULus Listed	Yes
Technical Information			
Connection	Back and side wire	Class	IG
Amperage	20 A	Environmental Conditions	Flammability: UL94 V2