

Turnlok® Plug 3-Wire 30A 250V Isolated Ground



## Features & Benefits

UL1449 (latest revision). (1.2 x 50: s 6000V, 8 x 20: s 3000A). 140 joules of energy absorption in each of the three modes.

9,000 amps current handling capability in each of three modes: line to neutral, line to ground, neutral to ground.

1 filtering capacitor for 7 to 1 average noise reduction.  
 Nominal let-through (suppressed) voltage in all 3 modes, 500V.

LED indicator light.

Response time less than 1 nanosecond for unmounted MOV.

Overcurrent protection in all 3 modes. Electronic components potted for electrical, mechanical and thermal stability. Thermal protection in all 3 modes.

Leakage current: 0.5 mA at 25: C/120VAC. 3 18mm super MOVs to suppress transients in all modes equally.

Common mode noise attenuation: 500 KHz to 30 MHz: up to 35 dB (50 ohm source impedance) Varistor voltage: 150V RMS.

Back and side wire capability including ground terminal.

Operating temperature: -40: C to 85: C (-40: F to 185: F)

Conforms to the latest revision ANSI/IEEE C62.41 (formerly IEEE 587), ANSI/IEEE C62.45.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007262988	Country Of Origin	United States
Application Sector	Industrial	Standard	UL Listed
Type	Plug Tail		

---

## Dimensions

---

Product Width US	2.2 in	Product Depth US	3.75 in
Product Height US	2.2 in		

---

## Listing Agencies / 3rd Party Agencies

---

cULus ListingNumber	146159	cULus Listed	Yes
---------------------	--------	--------------	-----

---

## Technical Information

---

Phase	Three	Number of Wires	3
Amperage	30 A	Number of Poles	Double Pole
Voltage	250.0 V		

---