

Turnlok® Single Receptacle 4-Wire 20A 3-Phase 250V Isolated Ground



Features & Benefits

UL1449 (latest revision). (1.2 x 50: s 6000V, 8 x 20: s 3000A).

9,000 amps current handling capability in each of three modes: line to neutral, line to ground, neutral to ground.

Nominal let-through (suppressed) voltage in all 3 modes, 500V.

Overcurrent protection in all 3 modes.

Thermal protection in all 3 modes.

3 18mm super MOVs to suppress transients in all modes : equally.

Varistor voltage: 150V RMS. Back and side wire capability including ground terminal.

Conforms to the latest revision ANSI/IEEE C62.41 (formerly IEEE 587), ANSI/IEEE C62.45.

140 joules of energy absorption in each of the three modes.

1 filtering capacitor for 7 to 1 average noise reduction.

LED indicator light. Response time less than 1 nanosecond for unmounted MOV.

Electronic components potted for electrical, mechanical and thermal stability.

Leakage current: 0.5 mA at 25: C/120VAC.

Common mode noise attenuation: 500 KHz to 30 MHz: up to 35 dB (50 ohm source impedance)

Operating temperature: -40: C to 85: C (-40: F to 185: F)

Specifications

General Info

Product Line	Pass & Seymour	Color	Orange
UPC Number	785007152210	Country Of Origin	Mexico
Number of Receptacles	1	Features	Indicator Lights

Outlet Type	Isolated Ground, Locking	Application Sector	Industrial
Wall Plate Included	No	Standard	UL Listed, FEDSPEC
Warranty Type	1-Year Limited Warranty		
Dimensions			
Product Width US	1.61 in	Product Depth US	1.19 in
Product Height US	2.29 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	140596	cULus Listed	Yes
Technical Information			
Connection Location	Back and Side	Phase	Three
Number of Wires	4	Amperage	20 A
Number of Poles	3-Way	Wire Size	14 - 10 AWG
Indoor/Outdoor	Indoor	NEMA Configuration Code	L15-20R
Wire Connection Type	Screw Terminals	Voltage	250.0 V