

Turnlok Single Receptacle 4wire 20amp 3phase 250volt Isolated Ground



## Features & Benefits

UL1449 (latest revision). (1.2 x 50: s 6000V, 8 x 20: s 3000A).

9,000 amps current handling capability in each of three modes: line to neutral, line to ground, neutral to ground.

Nominal let-through (suppressed) voltage in all 3 modes, 500V.

Overcurrent protection in all 3 modes.

Thermal protection in all 3 modes.

3 18mm super MOVs to suppress transients in all modes : equally.

Varistor voltage: 150V RMS. Back and side wire capability including ground terminal.

Conforms to the latest revision ANSI/IEEE C62.41 (formerly IEEE 587), ANSI/IEEE C62.45.

140 joules of energy absorption in each of the three modes.

1 filtering capacitor for 7 to 1 average noise reduction.

LED indicator light. Response time less than 1 nanosecond for unmounted MOV.

Electronic components potted for electrical, mechanical and thermal stability.

Leakage current: 0.5 mA at 25: C/120VAC.

Common mode noise attenuation: 500 KHz to 30 MHz: up to 35 dB [50 ohm source impedance]

Operating temperature: -40: C to 85: C [-40: F to 185: F]

## Specifications

### General Info

**Color** Orange

**UPC Number** 785007152210

**Countries Of Origin** Mexico

**Product Line** Pass & Seymour

**Application Sector** Industrial

**Standard** UL Listed

### Listing Agencies / 3rd Party Agencies

**cULus Listed** Yes

**cULus ListingNumber** 140596

### Technical Information

---

<b>Number of Poles</b>	3-Way
------------------------	-------

---

<b>Voltage</b>	250 V
----------------	-------

---

<b>Phase</b>	3
--------------	---

---

<b>Number of Wires</b>	4
------------------------	---

---