



Wattstopper
DLM Segment Network Wire, White
Part No. LM-MSTP-W



This type of wire connects low voltage devices (i.e., switches, occupancy sensors, photocells) to panels. It is #20 AWG wire that meets UL and NEC standards for Class 2 applications. Plenum rated wire meets plenum and riser requirements. Several types of multi-conductor low voltage wires are available for standard, pilot, locator, and multilevel switching or for connecting photocells to the LI control panels. This wire can also be used to wire relays remotely

Features & Benefits

Data communications wire provides communications between panels and signaling devices

Custom cut to specified lengths

Distance markings in foot increments

Low voltage component wire connects switches, sensors, and other low voltage devices to panels

Color-coded for streamlined installation

Specifications

General Info

Product Line	Wattstopper	Color	White
UPC Number	754182931903	Country Of Origin	United States
Product Series	LM-MSTP	Jacket Color	White
Application Sector	Commercial	Standard	UL, cUL
Warranty Type	5-Year	Type	Cable

Dimensions

Product Weight US	1.0 lb	Product Length US	1.0 FT
Cable Length	1 ft		

Technical Information

Jacket Material	PVC	Wire Gauge	22 AWG
Jacket Application	Plenum Rated	Shielded/Unshielded	Shielded
Conductor	1.5-Pair	Protocol	MS/TP
Jacket Rating	CL3P Rated, CMP Rated, FT6 Rated	Temperature Rating	75° C
Cable Diameter	0.185 in	Indoor/Outdoor	Indoor