



Every component of these locking connectors are built to offer the lowest installed cost and maximum durability. Quick-threaded assembly screws install four times faster than competitive products and backed-out screws come ready to wire. Rugged easy-to-grip nylon housing, clear thermoplastic terminal chambers as well as high-strength brass alloy contacts are all features of this premium Turnlok L1520C 4-Wire 20A 3-Phase 250V connector.

Features & Benefits

Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.

Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.

Raised ribs provide non-slip gripping profile for turning to lock and unlock.

Double dovetail design provides superior protection against cord pull-out forces.

Impact- and corrosion-resistant durable nylon 6 shell material.

Rounded back contour reduces snags and hang-ups on the job site.

Scalloped shell design provides non-slip gripping surface for insertion and withdrawal.

Visible stamped NEMA configuration and device rating.

New-design external cord grips provide visible assurance of safe and proper cord retention.

Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber.

Cord Diameter: 0.225 to 1.150 Inches

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007152012	Country Of Origin	Mexico
Receptacle Type	Locking	Application Sector	Industrial
Standard	UL Listed UL498, File Number E146159, FEDSPEC	Warranty Type	1-Year

Dimensions

Product Width US	2.2 in	Product Length US	3.33 in
------------------	--------	-------------------	---------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	146159	cULus Listed	Yes
---------------------	--------	--------------	-----

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Connection	TurnLok Receptacle	Number of Wires	4
Amperage	20 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Environmental Conditions	Flamability Rating UL94 V2
