



Wattstopper DLM Wired Network Bridge Module, USA Part No. LMBC-300-U



The LMBC-300 Digital Network Bridge provides a segment network connection for a group of Digital Lighting Management (DLM) local network devices. This enables individual DLM local networks to be aggregated into a larger system, which, in turn, can be remotely managed from a Network Controller or a building automation system (BAS).

Features & Benefits

Provides connectivity between a DLM local network and a BACnet compatible DLM segment network

Optional wiring harness for fast installation of multiple devices in close proximity

Class 2 device powered from DLM local network

Supports third party integration with BAS through BACnet MS/TP

MS/TP BACnet automatic configuration for DLM segment network eliminates the need for DIP switches

Plug n' Go™ automatically connects module with all devices on DLM local network

Specifications

General Info

Product Line	Wattstopper	Color	White
Finish	Glossy	UPC Number	754182933921
Country Of Origin	United States	Product Series	LMBC
Installation Location	Ceiling, Wall	Included	Din Rail Clip
Application Sector	Commercial	Standard	UL, RoHS, FCC part 15, BAA
Warranty Type	5-Year	Type	Bridge

Dimensions

Product Width US	2.8 in	Product Weight US	3.0 oz
Product Volume US	14.8 cu in	Product Depth US	1.7 in

Product Height US	3.1 in
-------------------	--------

Technical Information

Operating Temperature Min	32 °F	Compatibility	DLM Wired
---------------------------	-------	---------------	-----------

Number of Connections	3	Operating Temperature Max	158 °F
-----------------------	---	---------------------------	--------

Topology	Free Topology	Indicator	Device Status LED, Receive LED, Transmit LED
----------	---------------	-----------	--

Connector Type	MS/TP, RJ-45	Input Voltage	24 VDC
----------------	--------------	---------------	--------

Indoor/Outdoor	Indoor	Mounting Type	Inside 2-Gang J-Box, Surface
----------------	--------	---------------	------------------------------

Current Draw	30 mA	Operating Temperature	32°-158°F
--------------	-------	-----------------------	-----------

Operating Humidity	0-95% RH (Non-Condensing)	Storage Temperature	23° - 176° F
--------------------	---------------------------	---------------------	--------------
