



Wattstopper
Discontinued - Digital Dimming Wall Switch, 1 paddle, w/IR, Lt. Almond
Part No. LMDM-101-LA



The LMDM-101 Digital Dimming Wall Switch is a low voltage device for dimming control of one or more lighting loads. It is part of a Digital Lighting Management (DLM) system and can dim load(s) connected to DLM dimming room controllers and switch load(s) connected to DLM on/off room controllers.

Features & Benefits

- Low voltage switch for control of dimmable loads Plugs to other components using Cat 5e cable and RJ45 connectors eliminating wiring errors
- LED bar graph indicates relative light level of controlled load Active Dim feature enables temporary adjustment of any selected load
- IR transceiver for wireless configuration and remote control

Specifications

General Info

Product Line	Wattstopper	Color	Light Almond
UPC Number	754182929245	Country Of Origin	China
Product Series	LMDM	Switch Type	Push
Number of Switches	1	Application Sector	Commercial
Warranty Type	5-Year	Type	Dimmer, Switch

Dimensions

Product Width US	1.8 in	Product Weight US	0.2 lb
Product Volume US	11.8 cu in	Product Depth US	1.6 in

Product Height US	4.1 in
-------------------	--------

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Operating Temperature Min	0 °C	Compatibility	DLM Wired
---------------------------	------	---------------	-----------

Has Battery	No	Number of Connections	2
-------------	----	-----------------------	---

Operating Temperature Max	55 °C	Number of Buttons	1
---------------------------	-------	-------------------	---

Number of Rockers	0	Input Voltage	24 VDC
-------------------	---	---------------	--------

Indoor/Outdoor	Indoor	Mounting Type	J-Box
----------------	--------	---------------	-------

Current Draw	5 mA	Operating Temperature	0°-55°C, 32°-131°F
--------------	------	-----------------------	--------------------

Operating Humidity	5-95% RH (Non-Condensing)	Wire Connection Type	RJ-45
--------------------	---------------------------	----------------------	-------

Engraving Type	Blank
----------------	-------
