



Infinium M4 Cassettes are part of a complete fiber solution. When combined with matched Infinium Trunks and Infinium Patch Cable Assemblies the solution can enable industry leading pre-terminated performance and universal polarity for simple, fast and consistent and simplified installation. Compatible with Infinium HD-E Rack Mount Fiber Enclosure with M4 Drawer Face.

## Features & Benefits

- High Density: 12 or 24-fiber cassette compatible with Infinium HD M4 Enclosures
- Fiber Type: Supports either Single-mode OS2 or Multimode Infinium Ultra fiber
- LC adapter with Internal shutter: Provides eye safety by attenuating laser light when the mated connector is removed • 100% automatic shutter mechanism requiring no operator handling of the shutter door • Compatible with standard LC connectors • It keeps adapter's interior clean from dust • You can see the visible light through the adapter
- Infinium Core: Low Loss System: When combined with Infinium Core Trunks and Infinium Core Patch Cords • Single-mode total channel connection loss: 2.1 dB • Single-mode total channel connection return loss: 49 dB • Multimode total channel connection loss: 2.5 dB • Multimode total channel connection return loss: 19 dB
- Versatile Installation: Infinium Modular Panel enables mixed media installations
- Polarization: Universal
- Infinium Ultra: Ultra Low Loss System: When combined with Infinium Ultra Trunks and Infinium Ultra Patch Cords • Single-mode total channel connection loss: 1.2 dB • Single-mode total channel connection return loss: 49 dB • Multimode total channel connection loss: 1.0 dB • Multimode total channel connection return loss: 19 dB

## Specifications

### General Info

Product Line	Ortronics	UPC Number	662875031079
Country Of Origin	United States	Application Sector	Commercial
Standard	TIA-568-C.3	Type	Cassette

### Dimensions

Product Width US	4.24 in	Product Depth US	4.77 in
------------------	---------	------------------	---------

---

Product Height US	1.14 in
-------------------	---------

---

Additional Information

---

RoHS Conformant	Yes
-----------------	-----

---

Technical Information

---

Compatibility	Infinium High Density (HD) Enhanced Fiber Enclosure	Number of Ports	12
---------------	---	-----------------	----

---

Performance Level/Tier	Infinium Core
------------------------	---------------

---