




Wattstopper
LMCP 0-10V PANEL w/48-RELAY MAX CAPACITY
Part No. LMCP48-10V



The LMCP series panels are available for Dimming (LMCPx-10V) or Switched(LMCPx) control of lighting and plug loads. The panels can be networked together to enable automation through out an entire facility. The HDR panel relays respond to inputs from Digital Lighting Management (DLM) switches, occupancy sensors, daylight sensors, input modules and 0-10V outputs on dimming panel models.

Features & Benefits

Dimming panels dim 0-10V lighting loads as well as switch lighting and plug loads

Switching panels switch lighting and plug loads

Native BACnet communications for network control solutions

Easy setup via LMCT-100 handheld configuration tool

HDR relays include a switch for manual override even when panel is powered off

Compatible with Digital Lighting Management switches, sensors and input devices

99 control groups accessible via handheld configuration tool

Specifications

General Info

Product Line	Wattstopper	Color	Nickel
UPC Number	754182947508	Country Of Origin	United States
Product Series	LMCP	Installation Location	Enclosure, Wall
Application Sector	Commercial	Standard	UL 924, cUL, BAA, TAA, OSHPD Approved OSP-0257, PEP, ISO 14025:2010, ISO 14001, ISO 14040:2006, ISO 14044:2006, RoHS 2011/65/EC
Warranty Type	5-Year	Type	Relay Panel

Dimensions

Product Width US	24.0 in	Product Weight US	85.5 lb
Product Volume US	5126.4 cu in	Product Depth US	4.7 in
Product Height US	44.5 in		

Additional Information

Product Has Potential to Contribute to LEED Yes

Technical Information

Operating Temperature Min	32 °F	Timer Type	Event Based
Dimming Compatibility	0-10 V	Operating Temperature Max	140 °F
Topology	Free Topology	Number of Relays	48
Input Voltage	120/277/347 V	Line Frequency	50 Hz, 60 Hz
Indoor/Outdoor	Indoor	Operating Temperature	0°-60°C, 32°-140°F
Operating Humidity	5-95% RH (Non-Condensing)	Wire Connection Type	RJ-45